



From nanoparticles, nanorods to nanowalls: preparation and analysis of ZnO using hydrothermal approach for hydrophobic and UV photodetector applications

Raed A. Dheyab¹, Halder Abdulrah², Tahseen A. Alaridhee², Rasha S. Yousif², Zainab Abdulrah⁴, Ali H. Reshak^{2,5}, Zainab J. Sweah⁶, Nadiyah A. Abdullah², Mahr A. Jalal², and Mohammed Al-Fadhil⁷

¹ Chemical Engineering Department, College of Engineering, University of Basrah, Basra 61004, Iraq

² Department of Materials Science, Polymer Research Center, University of Basrah, Basra 61004, Iraq

³ Department of Petroleum Engineering, College of Engineering, University of Basrah, Basra 61004, Iraq

⁴ Department of Chemistry, Science College, University of Basrah, Basra 61004, Iraq

⁵ Physics Department, College of Science, University of Basrah, Basra 61004, Iraq

⁶ Department of Chemistry and Polymer Technology, Polymer Research Centre, University of Basrah, Basra 61004, Iraq

⁷ College of Science, University of Lincoln, Lincoln LN6 7TS, UK

Received: 10 August 2025

Accepted: 18 November 2025

© The Author(s), under exclusive license to Springer Science+Business Media, LLC, part of Springer Nature, 2025

ABSTRACT

This work investigates the synthesis of ZnO nanostructures with various aspect ratios, such as nanoparticles (NPs), nanorods (NRs), and nanowalls (NWs), by controlling the hexamethylenetetramine (HMT) concentrations via a hydrothermal approach for UV detectors and hydrophobic surfaces. The FE-SEM images revealed that the surface morphology of zinc oxide NPs, NRs, and NWs was well aligned and dispersed throughout the glass substrate. Hexagonal wurtzite ZnO was confirmed using X-ray diffraction (XRD). Apparently, rods and walls where growth well alignment highly reflect the oriented (002) plane onto the glass substrate, as depicted in FE-SEM analysis. Current–time (*i*–*T*) measurements verified the photodetector's performance and revealed a significant photocurrent enhancement under 365 nm UV light, reaching 45 μ A for the nanorods sample 1:0.5, achieving a 96% sensitivity, the highest of all samples tested. In addition, the vertical alignment of the 1:0.25 ZnO NRs enabled superhydrophobicity, resulting in a 162.40° contact angle. As a result, these findings confirm the value of the hydrothermal route for preparing different shapes of ZnO for advanced applications such as self-cleaning and UV detector.

Address correspondence to E-mail: maalidph@yahoo.co.uk